

Institut für Solartechnik SPF HSR Hochschule für Technik Rapperswil Oberseestrasse 10, CH-8640 Rapperswil Tel. +41 55 222 48 21, Fax +41 55 222 48 44 www.spf.ch

Test Report

ISO/EN 22975-3 Part 3: Absorber Surface Durability

Part A

The test allows the qualification of solar absorber coatings to be used in ventilated flat plate collectors with a maximum loss in system performance of 5% during 25 years of operation. The coating was tested according to ISO/EN 22975-3 Part 3 with regards to:

Part A: Stability with regards to high temperature

Test material

Commissioner:

ALMECO GmbH

Claude Breda Strasse 3

D-06406 Bernburg, Germany

Trade name:

TiNOX robust Al

Description:

Selective solar absorber:

PVD coating with protection and antireflection layer based on oxide ceramic / cermet absorber multilayer / adhesion layer / aluminium

substrate

Start of test:

December 2021

Completion of test:

May 2022

Expiration date:

May 2027

(The test result is no longer valid after substantial changes of the coating or substrate)

The test material has passed **part A** (**stability with regards to high temperature**) of the test according to ISO/EN 22975-3 and is qualified to be used in single glazed flat plate collectors with double-side AR coated glass.



Preliminary testing

Sample conditioning

According to clause 5.2 of the ISO 22975-3 standard, the optical properties of three as-received samples have been measured in order to determine the temperature for pre-conditioning by the use of table B.1 from the standard. The results are presented in Table 1.

Table 1: Optical properties of three as-received samples and pre-conditioning temperature

	Sample V1	Sample V2	Sample V3	Mean value
Solar absorptance, α _s	0.932	0.932	0.932	0.932
Emittance, ε ₁₀₀	0.030	0.032	0.033	0.032
Temperature to be applied	for pre-conditi	oning of the sa	mples	214°C

Qualification for testing

In total, 18 samples have been pre-conditioned by tempering for 5 hours at the temperature given in Table 1. The optical properties after tempering were determined and they are presented in Table 2. The value of the solar absorptance and thermal emittance was calculated as specified in clause 5.3 and 5.4 from ISO/EN 22975-3.

Table 2: Mean values of the optical properties of 18 samples after pre-conditioning

	Solar absorptance, α _s	Emittance, ε ₁₀₀
Mean value	0.932	0.034
Standard deviation	0.001	0.002
Minimum value	0.930	0.030
Maximum value	0.935	0.037

After pre-conditioning, an adhesion test according to ISO 2409 (for soft samples) has been applied to three of the samples. The results are presented in Table 3.

Table 3: Result of the adhesion test performed on three samples after pre-conditioning

	Sample 1	Sample 2	Sample 3
Adhesion test result grade	0	0	0

According to clause 4.2 and 4.3 of the ISO 22975-3 standard, the test specimens are <u>qualified</u> <u>for testing</u>. The standard deviation for solar absorptance and thermal emittance is less than 0.01 and 0.04, respectively, and as the adhesion test of the three samples was leading to a result grade \leq 1 (Table 3).

Date: 12.05.2022 Commissioner: ALMECO GmbH page 2 of 5

From the mean values of the optical properties from Table 2, the expected maximum absorber surface temperature (T_{max}) has been determined according to table B.1 from ISO/EN 22975-3. This is needed to evaluate the testing temperature levels for qualification (Table 4) by the use of table B.2 from ISO/EN 22975-3.

Table 4: Expected maximum absorber surface temperature (T_{max}) and testing temperature levels to be used for qualification testing

	Temperature [°C]
maximum absorber surface temperature T _{max}	214
first testing temperature T₁	291

Tests for assessing the thermal stability of absorber surfaces

According clause 6.4.3 of the standard, three samples were exposed to the first testing temperature level T_1 for a testing time up to 600 h or until PC \geq 0.05. The optical properties determined after different testing times (18, 36, 75, 150, 300 and 600 h) are shown in Table 5.

Table 5: PC mean value of three samples after testing at T₁

Time of exposure	18 h	36 h	75 h	150 h	300 h	600 h
PC	0.001	-0.002	0.000	-0.001	-0.005	-0.004

According to clause 7.4.2 of the ISO/EN 22975-3:2014, the absorber coating is qualified with regards to its thermal stability if after testing at the temperature level T_1 for a testing time t_1 of 600h, the $PC(t_1) \le 0.015$ and the adhesion test of the three samples was leading to a result grade ≤ 1 .

Table 6: Results of the adhesion tests performed on three samples after 600 h of testing at temperature T_1 .

	Sample 1	Sample 2	Sample 3
Adhesion test result grade	0	0	0

As the absorber coating meets the above required conditions, the test material has passed part A (stability with regards to high temperature) and it is qualified to be used in single glazed flat plate collectors.

SPF Institute for Solar Technology Rapperswil, May 2022

Mihaela Dudita SPF Project manager Stefan Brunold SPF Deputy Head of Institute

Date: 10.05.2022 Commissioner: ALMECO GmbH page 3 of 5



Annex

Deviations from the testing method

None.

Solar absorptance (α_s)

Hemispherical reflectance was measured with a BRUKER VERTEX 80 UV-VIS-MIR Fourier-transform spectrophotometer equipped with a 150 mm integrating sphere. 'Spectralon' diffuse reflectance standard was used as reflectance reference. The solar absorptance was calculated for airmass 1.5 using the hemispherical solar spectral irradiance data as described in ISO 9050:2003.

Thermal emittance (ε₁₀₀)

For thermal emittance evaluation, the same instrument was used to measure the hemispherical reflectance, but with an 'Infragold' reflectance standard as a reference. The black body radiation spectrum for a temperature of 100°C (373 K) was used for thermal emittance calculation. It was generated according to Planck's law of black body radiation.

Performance criterion, PC

The performance criterion, which shows the changes in performance of an absorber surface in terms of solar absorptance and thermal emittance, was calculated using Eq. 1. For classification of the durability of the absorber coating surface according to the ISO/EN 22975-3:2014 standard, the following performance requirement is applied.

$$PC = -\Delta \alpha_s + 0.50 \Delta \epsilon \le 0.05$$

Eq. 1

where: $\Delta \alpha_s$ is the change in the solar absorptance defined as:

 $\Delta \alpha_s = \alpha_{s,t} - \alpha_{s,i}$, with $\alpha_{s,t}$ equal to the value of the solar absorptance at the actual time of the test, and with $\alpha_{s,i}$ equal to the initial value of solar absorptance.

and $\Delta \varepsilon$ is the change in the thermal emittance:

 $\Delta \varepsilon = \varepsilon_t - \varepsilon_i$ with ε_t equal to the value of the thermal emittance at the actual time of the test and with ε_t equal to the initial value of thermal emittance.

Testing chamber

A Snijstaal circulating air oven (type P2000) was used for conditioning the samples and for the high temperature exposure. The temperatures were measured with a calibrated (± 1 K) Pt-100 sensor.

Date: 10.05.2022 Commissioner: ALMECO GmbH page 4 of 5



Institut für Solartechnik SPF HSR Hochschule für Technik Rapperswil Oberseestrasse 10, CH-8640 Rapperswil Tel. +41 55 222 48 21, Fax +41 55 222 48 44 www.spf.ch

Detailed results

4. ALMRZ11200XZ 0.932 0.034 0.032 e.ton a.g. a.g. a.g.	ž	Nr. Sample code	Refe	Reference	5h @ 215°C	215°C	18	18h	36h	ŗ,	75h	ų,	15	150h	300h	0h	600h	Jh
ALMR211200xZ 0.932 0.030 0.931 0.032 0.031 0.032 0.031 0.034			ၓ	£100	ຮ [ຶ]	£100	ອຶ	£100	α	£100	రో	£100	ຶ່ນ	8100	້ອ້	8100	ర	£100
ALMR211201xZ 0.932 0.033 0.033 0.033 0.033 0.033 0.031 0.033 0.031 0.033 0.031 0.033 0.031 0.033 0.031 0.033 0.031 0.032 0.031 0.032 0.031 0.032 0.031 0.032 0.031 0.032 0.031 0.032 0.031 0.032 0.031 0.032 0.031 0.032 0.031 0.032 0.031 0.032 0.041 0.934 0.041 0.934 0.041 0.934 0.041 0.934 0.042 0.936 0.041 0.934 0.042 0.934 0.042 0.934 0.041 0.934 0.042 0.936 0.042 0.936 0.042 0.936 0.042 0.936 0.042 0.936 0.042 0.936 0.042 0.936 0.042 0.936 0.042 0.936 0.042 0.936 0.042 0.936 0.042 0.936 0.042 0.936 0.042 0.936 0.042 0.936 0.042	.	ALMR211200xZ	0.932	0.030	0.931	0.032									,		n	
ALMR211202xZ 0.933 0.931 0.033 0.936 0.031 6 6 6 6 6 6 6 6 6 6 6 6 6 6 6 6 6 6 7 6 7 6 7 <	5	ALMR211201xZ	0.932	0.032	0.931	0.034												
ALMR211203xZ O.935 O.031 O.936 O.031 O.936 O.041 O.934 O.042 O.936 O.041 O.934 O.041 O.936 O.041 O.937 O.042 O.936	က်	ALMR211202xZ	0.932	0.033	0.931	0.033												
ALMR211206xZ 0.931 0.032 6.034 0.042 0.936 0.041 0.934 0.042 0.936 0.041 0.934 0.042 0.936 0.041 0.934 0.042 0.936 0.041 0.934 0.042 0.936 0.041 0.934 0.042 0.936 0.041 0.934 0.042 0.936 0.041 0.934 0.042 0.934 0.041 0.934 0.042 0.934 0.041 0.934 0.041 0.934 0.042 0.934 0.040 0.934 0.042 0.934 0.040 0.934 0.042 0.934 0.040 0.934 0.042 0.934 0.040 0.934 0.042 0.934 0.042 0.934 0.042 0.934 0.042 0.934 0.042 0.934 0.042 0.934 0.042 0.934 0.042 0.934 0.042 0.934 0.042 0.934 0.042 0.934 0.042 0.934 0.042 0.934 0.042 0.934 0.042 0.934	4.	ALMR211203xZ			0.935	0.031												
ALMR211206xZ 0.933 0.030 0.934 0.042 0.936 0.041 0.934 0.042 0.936 0.041 0.934 0.041 0.934 0.042 0.936 0.041 0.936 0.042 0.936 0.041 0.936 0.042 0.936 0.042 0.936 0.042 0.936 0.042 0.936 0.041 0.937 0.042 0.936 0.042 0.936 0.041 0.937 0.040 0.937 0.040 0.937 0.040 0.937 0.040 0.937 0.040 0.937 0.040 0.937 0.040 0.937 0.040 0.937 0.040 0.937 0.040 0.937 0.040 0.937 0.040 0.937 0.040 0.937 0.040 0.934 0.041 0.934 0.035	5.	ALMR211204xZ			0.931	0.032			-									
ALMR211206xZ 0.930 0.031 0.934 0.042 0.936 0.041 0.936 0.041 0.936 0.042 0.936 0.042 0.936 0.041 0.936 0.042 0.936 0.042 0.936 0.042 0.936 0.042 0.936 0.042 0.936 0.042 0.936 0.042 0.937 0.040 0.936 0.042 0.937 0.040 0.937 0.040 0.937 0.040 0.937 0.040 0.937 0.040 0.937 0.040 0.937 0.040 0.937 0.040 0.937 0.040 0.937 0.037 0.037 0.037 0.037 0.037 0.037 0.037 0.037 0.037 0.037 0.037 0.037 0.037 0.033 0.036 0.034 0.034 0.034 0.034 0.034 0.034 0.034 0.034 0.034 0.034 0.034 0.034 0.034 0.034 0.040 0.037 0.034 0.034 0.034 0.040 0.034 0.040 0.037 0.034 0.034 0.034 0.040 0.034 0.040	<u>ن</u>	ALMR211205xZ			0.933	0.030						***************************************						
ALMR211207xZ ALMR211207xZ 0.931 0.035 0.041 0.937 0.042 0.934 0.040 0.936 0.040 0.937 0.040 0.936 0.040 0.937 0.040 0.936 0.042 0.937 0.040 0.939 0.042 0.939 0. 4LMR211209xZ 0.930 0.035 0.035 0.035 0.035 0.041 0.940 0.040 <t< td=""><td>7.</td><td>ALMR211206xZ</td><td></td><td></td><td>0.930</td><td>0.031</td><td>0.934</td><td>0.042</td><td>0.936</td><td>0.041</td><td>0.934</td><td>0.041</td><td>0.936</td><td>0.042</td><td>0.936</td><td>0.033</td><td>0.935</td><td>0.034</td></t<>	7.	ALMR211206xZ			0.930	0.031	0.934	0.042	0.936	0.041	0.934	0.041	0.936	0.042	0.936	0.033	0.935	0.034
ALMR211208xZ 0.933 0.033 0.936 0.041 0.940 0.040 0.937 0.040 0.939 0.042 0.939 0.930 0.035	ထ	ALMR211207xZ			0.931	0.035	0.933	0.041	0.937	0.042	0.934	0.040	0.936	0.042	0.936	0.033	0.935	0.033
ALMR211209xZ 0.930 0.035 6.035 6.030 6.035 6.035 6.035 6.035 6.035 6.035 6.035 6.035 6.035 6.035 6.035 6.037 6.032 6.035	တ်	ALMR211208xZ			0.933	0.033	0.936	0.041	0.940	0.040	0.937	0.040	0.939	0.042	0.939	0.034	0.938	0.033
ALMR211210xZ 0.930 ALMR211211xZ 0.931 ALMR211213xZ 0.931 ALMR211214xZ 0.932 ALMR211216xZ 0.932 ALMR211216xZ 0.932 ALMR211216xZ 0.932	10.	ALMR211209xZ			0.930	0.035									-			
ALMR211211xZ 0.931 ALMR211213xZ 0.931 ALMR211213xZ 0.932 ALMR211215xZ 0.932 ALMR211216xZ 0.933 ALMR211216xZ 0.932 ALMR211217xZ 0.932	Ξ.	ALMR211210xZ			0.930	0.035						***************************************						***************************************
ALMR211213xZ 0.933 ALMR211213xZ 0.931 ALMR211214xZ 0.932 ALMR211216xZ 0.933 ALMR211216xZ 0.932 ALMR211217xZ 0.932	12.	ALMR211211xZ			0.931	0.035						***************************************						
ALMR211213xZ ALMR211214xZ ALMR211215xZ ALMR211216xZ ALMR211216xZ ALMR211217xZ O.933	13.	ALMR211212xZ			0.933	0.036												
ALMR211215xZ ALMR211216xZ ALMR211216xZ ALMR211217xZ O.933	14.	ALMR211213xZ			0.931	0.035												
ALMR211215xZ ALMR211216xZ ALMR211217xZ 0.933	15.	ALMR211214xZ			0.932	0.037												
ALMR211216xZ ALMR211217xZ 0.931	16.	ALMR211215xZ			0.933	0.035												
ALMR211217xZ 0.931	17.	ALMR211216xZ			0.932	0.035									***************************************			
	18.	ALMR211217xZ			0.931	0.034									***************************************			***************************************

Commissioner ALMECO GmbH Handled by **Mihaela Dudita**

10.05.2022 Date

Page 5 of 5