

Institut für Solartechnik SPF HSR Hochschule für Technik Rapperswil Oberseestrasse 10, CH-8640 Rapperswil Tel. +41 55 222 48 21, Fax +41 55 222 48 44 www.spf.ch

#### **Test Report**

ISO 22975-3 Part 3: Absorber Surface Durability

Part B

The test allows the qualification of solar absorber coatings to be used in ventilated flat plate collectors with a maximum loss in system performance of 5% during 25 years of operation. The coating was tested according to ISO/EN 22975-3 Part 3 with regards to:

Part B: Stability with regards to high humidity and condensation

**Test material** 

Commissioner:

**ALMECO GmbH** 

Claude Breda Strasse 3

D-06406 Bernburg, Germany

Trade name:

TiNOX robust Al

Description:

Selective solar absorber:

PVD coating with protection and antireflection layer based on oxide

ceramic / cermet absorber multilayer / adhesion layer / aluminium

substrate

Start of test:

December 2021

Completion of test:

May 2022

Expiration date:

May 2027

(The test result is no longer valid after substantial changes of the coating or substrate)

#### **Test results**

The test material has passed **part B** (stability with regards to high humidity and condensation) of the test according to ISO 22975-3 and it is qualified to be used in single glazed flat plate collectors.



#### **Preliminary Testing**

#### Sample conditioning

According to clause 5.2 of the ISO 22975-3 standard, the optical properties of three as-received samples have been measured in order to determine the temperature for pre-conditioning by the use of Table B.1 from the standard. The results are presented in Table 1.

Table 1: Optical properties of three as-received samples and pre-conditioning temperature

|                                   | Sample V1       | Sample V2       | Sample V3 | Mean value |
|-----------------------------------|-----------------|-----------------|-----------|------------|
| Solar absorptance, α <sub>s</sub> | 0.932           | 0.932           | 0.932     | 0.932      |
| Emittance, ε <sub>100</sub>       | 0.030           | 0.032           | 0.033     | 0.032      |
| Temperature to be applied         | for pre-conditi | oning of the sa | mples     | 214°C      |

#### Qualification for testing

In total, 18 samples have been pre-conditioned by tempering for 5 hours at the temperature given in Table 1. The optical properties after tempering were determined and they are presented in Table 2. The value of the solar absorptance and thermal emittance was determined for each of the 18 test samples as specified in clause 5.3 and 5.4 from ISO/EN 22975-3.

Table 2: Mean values of the optical properties of 18 samples after pre-conditioning

|                    | Solar absorptance, α <sub>s</sub> | Emittance, ε <sub>100</sub> |
|--------------------|-----------------------------------|-----------------------------|
| Mean value         | 0.932                             | 0.034                       |
| Standard deviation | 0.001                             | 0.002                       |
| Minimum value      | 0.930                             | 0.030                       |
| Maximum value      | 0.935                             | 0.037                       |

After pre-conditioning, an adhesion test according to ISO 2409 (for soft samples) has been applied to three of the samples. The results are presented in Table 3.

Table 3: Result of the adhesion test performed on three samples after pre-conditioning

|                            | Sample 1 | Sample 2 | Sample 3 |
|----------------------------|----------|----------|----------|
| Adhesion test result grade | 0        | 0        | 0        |

According to clause 4.2 and 4.3 of the ISO 22975-3 standard, the test specimens are <u>qualified</u> <u>for testing</u>. The standard deviation for solar absorptance and thermal emittance is less than 0.01 and 0.04, respectively, and the adhesion test of the three samples was leading to a result grade  $\leq 1$ .

Date: 10.05.2022 Commissioner: ALMECO GmbH page 2 of 5



### Tests for determining the resistance to condensed water of absorber surfaces

According to the clause 7.4.1 of the ISO 22975-3 standard, three tempered samples were exposed to the first testing temperature level  $T_1$  = 40°C for a testing time up to 600 h or until PC  $\geq$  0.05. Time  $t_1$  is defined to be the latest testing time with PC  $\leq$  0.05. The optical properties determined after different testing times (18, 36, 75, 150, 300 and 600 h) and the value of  $t_1$  are presented in Table 4.

Table 4: PC mean value of three samples after testing at  $T_1 = 40^{\circ}$ C and identification of  $t_1$ 

| Time of exposure | 18 h  | 36 h  | 75 h  | 150 h | 300 h  | 600 h  |
|------------------|-------|-------|-------|-------|--------|--------|
| PC               | 0.003 | 0.002 | 0.003 | 0.001 | -0.002 | -0.004 |
| t <sub>1</sub> = |       |       | 600   | 0 h   |        |        |

According to the clause 7.4.2 of the ISO 22975-3 standard, the absorber coating is qualified with regards to its stability against high humidity and condensation if after testing at temperature level  $T_1$  for a testing time  $t_1$  = 600h:

- the PC(t₁) ≤ 0.015 (see Table 3) and
- the adhesion test of the three tested samples at T₁ was leading to a result grade ≤ 1.

Table 5: Results of the adhesion tests performed on three samples after the longest testing period at testing temperature  $T_1$ 

|                            | Sample 1 | Sample 2 | Sample 3 |
|----------------------------|----------|----------|----------|
| Adhesion test result grade | 0        | 0        | 0        |

As the absorber coating meets the required conditions, the test material has passed part B (stability with regards to high humidity and condensation) according to ISO 22975-3 and it is qualified to be used in single glazed flat plate collectors.

SPF Institute for Solar Technology Rapperswil, May 2022

Mihaela/Dudita

Stefan Brunold

SPF/Deputy Head of Institute

Date: 10.05.2022 Commissioner: ALMECO GmbH page 3 of 5



#### Annex

#### Deviations from the testing method

None.

#### Solar absorptance, $\alpha_s$

Hemispherical reflectance was measured with a BRUKER VERTEX 80 UV-VIS-MIR Fourier-transform spectrophotometer equipped with an 150 integrating sphere. 'Spectralon' diffuse reflectance standard was used as a reflectance reference. The solar absorptance was calculated for airmass 1.5 using the hemispherical solar spectral irradiance data as described in ISO 9050:2003.

#### Thermal emittance, ε<sub>100</sub>

For thermal emittance evaluation, the same instrument was used to measure the hemispherical reflectance, but with an 'Infragold' reflectance standard as a reference. The black body radiation spectrum for a temperature of 100°C (373 K) was used for the thermal emittance calculation. It was generated according to Planck's law of black body radiation.

#### Performance criterion, PC

The performance criterion, which shows the changes in performance of an absorber surface in terms of solar absorptance and thermal emittance, was calculated using Eq. 1. For classification of the durability of the absorber surface, the following performance requirement is applied, according to the ISO/EN 22975-3:2014 standard:

PC = 
$$-\Delta \alpha_s + 0.50 \Delta \epsilon \le 0.05$$

Eq. 1

where:  $\Delta \alpha_s$  is the change in solar absorptance, defined as:

 $\Delta \alpha_s = \alpha_{s,t} - \alpha_{s,i}$ , where  $\alpha_{s,t}$  is the solar absorptance at the actual time of the test, and  $\alpha_{s,i}$  represents the initial value of solar absorptance.

and  $\Delta \epsilon$  is the change in thermal emittance, defined as:

 $\Delta \varepsilon = \varepsilon_t - \varepsilon_i$  where  $\varepsilon_t$  is the thermal emittance at the actual time of the test and  $\varepsilon_i$  represents the initial value of thermal emittance.

#### **Testing chambers**

A CTS humidity cabinet (type CL-40/350/S) was used for the condensation tests. The samples were mounted on a water cooled metal sample holder, which was tilted 45°. The temperature of the samples was measured with a calibrated ( $\pm$  1°C) Pt-100 sensor. The temperature of the cabinet was 5°C higher than the sample temperature. The humidity inside the cabinet was 95% RH. The samples were electrically insulated from the sample holder by a Teflon coating.

Date: 10.05.2022 Commissioner: ALMECO GmbH page 4 of 5



# SPF SOLARTECHNIK

Institut für Solartechnik SPF HSR Hochschule für Technik Rapperswil Oberseestrasse 10, CH-8640 Rapperswil Tel. +41 55 222 48 21, Fax +41 55 222 48 44 www.spf.ch

## **Detailed Results**

| ALMR211200xZ         Ω <sub>s</sub> ε100         α <sub>s</sub> ε100         α <sub>s</sub> ε100         α <sub>s</sub> ALMR211200xZ         0.932         0.030         0.931         0.034         6.034         6.034         6.034         6.034         6.034         6.034         6.034         6.034         6.033         6.031         6.033         6.033         6.033         6.033         6.033         6.033         6.033         6.033         6.031         6.033         6.034         6.033         6.034         6.033         6.034         6.033         6.034         6.033         6.034         6.033         6.034         6.033         6.040         6.033         6.040         6.033         6.040         6.033         6.041         6.033         6.041         6.033         6.041         6.033         6.041         6.033         6.041         6.033         6.041   | ž            | Sample code  | Refe           | Reference | 2h @  | 5h @ 215°C | 18h            | ų,    | 36h   | 'n    | 1/2   | 75h                                     | 15    | 150h  | 300h       | чc                                      | 4009  | 0h                                      |
|--|--------------|--------------|----------------|-----------|-------|------------|----------------|-------|-------|-------|-------|---|-------|-------|------------|---|-------|---|
| ALMR211200xZ       0.932       0.030       0.931       0.032         ALMR211201xZ       0.932       0.032       0.931       0.034         ALMR211202xZ       0.932       0.033       0.931       0.033         ALMR211203xZ       0.932       0.031       0.032         ALMR211206xZ       0.933       0.030       0.031         ALMR211208xZ       0.931       0.035       0.035         ALMR211209xZ       0.933       0.035       0.035         ALMR211210xZ       0.931       0.035       0.035         ALMR211211xZ       0.933       0.036       0.035         ALMR21121xZ       0.933       0.036       0.036         ALMR21121xZ       0.933       0.036       0.035         ALMR21121xZ       0.933       0.036       0.037         ALMR21121xZ       0.933       0.036       0.037         ALMR21121xZ       0.933       0.036       0.040         ALMR21121xZ       0.933       0.036       0.040         ALMR211216xZ       0.933       0.035       0.040         ALMR211216xZ       0.933       0.035       0.040         ALMR211216xZ       0.933       0.035       0.040 <th>70</th> <th></th> <th><sub>ອ</sub>ຶ</th> <th>8100</th> <th>ອຶ</th> <th>£100</th> <th>ອ<sup>ຶ</sup></th> <th>£100</th> <th>ອຶ</th> <th>8100</th> <th>ຶ່</th> <th>2100</th> <th>້ຶ້</th> <th>£100</th> <th><b>ອ</b>້</th> <th>£100</th> <th>ຮ້</th> <th>£100</th>  | 70           |              | <sub>ອ</sub> ຶ | 8100      | ອຶ    | £100       | ອ <sup>ຶ</sup> | £100  | ອຶ    | 8100  | ຶ່    | 2100                                    | ້ຶ້   | £100  | <b>ອ</b> ້ | £100                                    | ຮ້    | £100                                    |
| ALMR211201xZ       0.932       0.032       0.931       0.033         ALMR211202xZ       0.932       0.033       0.931       0.033         ALMR211203xZ       0.932       0.031       0.032         ALMR211206xZ       0.933       0.032       0.031         ALMR211206xZ       0.933       0.035       0.031         ALMR211209xZ       0.933       0.035       0.035         ALMR211210xZ       0.930       0.035       0.035         ALMR21121xZ       0.931       0.035       0.035         ALMR21121xZ       0.931       0.035       0.035         ALMR211214xZ       0.933       0.035       0.035         ALMR211216xZ       0.933       0.035       0.037         ALMR211216xZ       0.933       0.035       0.037         ALMR211216xZ       0.933       0.035       0.037         ALMR211216xZ       0.933       0.035       0.041       0.933         ALMR211216xZ       0.932       0.035       0.041       0.933         ALMR211216xZ       0.932       0.035       0.041       0.933  | <del>-</del> | ALMR211200xZ | 0.932          | 0.030     | 0.931 | 0.032      |                |       |       |       |       |   |       |       | )          |   | ,     |   |
| ALMR211202xZ ALMR211203xZ ALMR211203xZ ALMR211205xZ ALMR211206xZ ALMR211206xZ ALMR211208xZ ALMR211208xZ ALMR211210xZ ALMR211210xZ ALMR21121xZ ALMR21121xZ ALMR21121xZ ALMR21121xZ ALMR21121xZ ALMR21121xZ ALMR211214xZ ALMR211214xZ ALMR211214xZ ALMR211216xZ ALMR211214xZ ALMR211216xZ ALMR211217xZ ALMR211217x | 7            | ALMR211201xZ | 0.932          | 0.032     | 0.931 | 0.034      |                |       |       |       |       |   |       |       |            |   |       |   |
| ALMR211203xZ ALMR211204xZ ALMR211206xZ ALMR211206xZ ALMR211206xZ ALMR211209xZ ALMR211210xZ ALMR211210xZ ALMR211210xZ ALMR211211xZ ALMR211214xZ ALMR211214xZ ALMR211216xZ ALMR211216xZ ALMR211214xZ ALMR211216xZ ALMR2 | က်           | ALMR211202xZ | 0.932          | 0.033     | 0.931 | 0.033      |                |       |       |       |       |   |       |       |            |   |       |   |
| ALMR211205xZ ALMR211205xZ ALMR211206xZ ALMR211207xZ ALMR211209xZ ALMR211210xZ ALMR211212xZ ALMR211213xZ ALMR211215xZ ALMR211216xZ ALMR2 | 4.           | ALMR211203xZ |                |           | 0.935 | 0.031      |                |       |       |       |       |   |       |       |            |   |       |   |
| ALMR211205xZ ALMR211206xZ ALMR211206xZ ALMR211207xZ ALMR211209xZ 0.933 0.035 0.930 0.035 0.930 0.035 0.931 0.035 0.931 0.035 0.931 0.035 0.931 0.035 0.931 0.035 0.931 0.035 0.931 0.035 0.931 0.035 0.932 0.037 0.933 0.036 0.933 0.036 0.933 0.036 0.933 0.036 0.933 0.037 0.933 0.037 0.037 0.933 0.035 0.040 0.933 0.933 0.035 0.041 0.933 0.933 0.034 0.932 0.041 0.933   | 5.           | ALMR211204xZ |                |           | 0.931 | 0.032      |                |       |       |       |       |   |       |       |            |   |       |   |
| ALMR211206xZ       0.930       0.031         ALMR211207xZ       0.931       0.035         ALMR211208xZ       0.933       0.035         ALMR211210xZ       0.930       0.035         ALMR211211xZ       0.931       0.035         ALMR211213xZ       0.933       0.036         ALMR211214xZ       0.933       0.035         ALMR211216xZ       0.933       0.035         ALMR211215xZ       0.933       0.035         ALMR211216xZ       0.933       0.035         0.932       0.035       0.041       0.933  | 9            | ALMR211205xZ |                |           | 0.933 | 0.030      |                |       |       |       |       |   |       |       |            |   |       |   |
| ALMR211207xZ ALMR211208xZ ALMR211209xZ 0.933 0.035 0.930 0.035 0.930 0.035 0.931 0.035 0.931 0.035 0.931 0.035 0.931 0.035 0.932 0.035 0.932 0.037 0.933 0.040 0.934 0.933 0.035 0.041 0.933 0.932 0.035 0.041 0.933   | 7.           | ALMR211206xZ |                |           | 0.930 | 0.031      |                |       |       |       |       |   |       |       |            |   |       |   |
| 0.933       0.033         0. ALMR211209xZ       0.930       0.035         1. ALMR211210xZ       0.931       0.035         2. ALMR211212xZ       0.933       0.036         3. ALMR211213xZ       0.933       0.035         6. ALMR211215xZ       0.932       0.037         7. ALMR211216xZ       0.933       0.035       0.933       0.040       0.934         7. ALMR211216xZ       0.932       0.035       0.035       0.041       0.933         8. ALMR211217xZ       0.932       0.035       0.035       0.041       0.933  | ω.           | ALMR211207xZ |                |           | 0.931 | 0.035      |                |       |       |       |       |   |       |       |            |   |       |   |
| ALMR211209xZ       0.930       0.035         ALMR211210xZ       0.931       0.035         ALMR211212xZ       0.931       0.036         ALMR211213xZ       0.931       0.036         ALMR211214xZ       0.932       0.037         ALMR211216xZ       0.933       0.035         ALMR211216xZ       0.933       0.035         ALMR211216xZ       0.932       0.035         ALMR211216xZ       0.932       0.035         ALMR211216xZ       0.932       0.035  | တ်           | ALMR211208xZ |                |           | 0.933 | 0.033      |                |       |       |       |       | *************************************** |       |       |            |   |       |   |
| ALMR211210xZ       0.930       0.035         ALMR211212xZ       0.931       0.035         ALMR211213xZ       0.931       0.036         ALMR211214xZ       0.932       0.037         ALMR211216xZ       0.933       0.035       0.940       0.934         ALMR211216xZ       0.932       0.035       0.040       0.934         ALMR211216xZ       0.932       0.035       0.041       0.933   | 10.          | ALMR211209xZ |                |           | 0.930 | 0.035      |                |       |       |       |       |   |       |       |            |   |       |   |
| ALMR211211xZ       0.931       0.035         ALMR211212xZ       0.933       0.036         ALMR211213xZ       0.931       0.035         ALMR211214xZ       0.932       0.037         ALMR211216xZ       0.933       0.035       0.933       0.040       0.934         ALMR211216xZ       0.932       0.035       0.932       0.041       0.933  | Έ.           | ALMR211210xZ |                |           | 0.930 | 0.035      |                |       |       |       |       |   |       |       |            |   |       |   |
| ALMR211212xZ       0.933       0.036         ALMR211213xZ       0.931       0.035         ALMR211214xZ       0.932       0.037         ALMR211216xZ       0.933       0.035       0.040       0.934         ALMR211216xZ       0.932       0.035       0.041       0.933         ALMR211216xZ       0.932       0.035       0.041       0.933  | 12.          | ALMR211211xZ |                |           | 0.931 | 0.035      |                |       |       |       |       |   |       |       |            |   |       |   |
| ALMR211213xZ       0.931       0.035       0.037         ALMR211214xZ       0.932       0.037       0.934         ALMR211216xZ       0.933       0.035       0.933       0.040       0.934         ALMR211216xZ       0.932       0.035       0.932       0.041       0.933  | 13.          | ALMR211212xZ |                |           | 0.933 | 0.036      |                |       |       |       |       |   |       |       |            | *************************************** |       |   |
| ALMR211216xZ ALMR211216xZ ALMR211216xZ ALMR211217xZ ALMR2 | 4.           | ALMR211213xZ |                |           | 0.931 | 0.035      |                |       |       |       |       |   |       |       |            |   |       |   |
| ALMR211216xZ ALMR211216xZ ALMR211217xZ ALMR211217xZ ALMR211217xZ ALMR211217xZ ALMR211217xZ ALMR211217xZ ALMR211217xZ   | 15.          | ALMR211214xZ |                |           | 0.932 | 0.037      |                |       |       |       |       |   |       |       |            |   |       | *************************************** |
| ALMR211216xZ 0.035 0.035 0.041 0.933 ALMR211217xZ 0.031 0.034 0.032 0.041 0.033  | 16.          | ALMR211215xZ |                |           | 0.933 | 0.035      | 0.933          | 0.040 | 0.934 | 0.040 | 0.934 | 0.043                                   | 0.935 | 0.039 | 0.935      | 0.033                                   | 0.941 | 0.042                                   |
| ALMR211217x7   | 17.          | ALMR211216xZ |                |           | 0.932 | 0.035      | 0.932          | 0.041 | 0.933 | 0.041 | 0.933 | 0.043                                   | 0.934 | 0.042 | 0.934      | 0.036                                   | 0.940 | 0.041                                   |
|  | 18.          | ALMR211217xZ |                |           | 0.931 | 0.034      | 0.932          | 0.041 | 0.933 | 0.040 | 0.933 | 0.041                                   | 0.934 | 0.042 | 0.934      | 0.035                                   | 0.938 | 0.044                                   |

Commissioner ALMECO GmbH

Mihaela Dudita Handled by